
INDUSTRIAL SPEC GRADE TURNLOK® 20A NON-NEMA 3-WIRE CONNECTOR, BLACK BACK, WHITE FRONT BODY

7313SS | [Pass & Seymour](#)



FEATURES & BENEFITS

Rely on Pass & Seymour Turnlok® portable power solutions for all your demanding jobsite applications that require temporary power.



- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

SPECIFICATIONS

GENERAL INFO

Color: Black, White
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121403

TECHNICAL INFORMATION

Amps: 20A
Volts: 125/250V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

