

# Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond

26352LA



Heavy-Duty Decorator Spec Grade Duplex  
Receptacle Back & Side Wire 20amp  
125volt Light Almond



## features & benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## specifications

**General Info**

Color: light almond  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: Back, Side Wire  
Style: Decorator

**Listing Agencies/Third Party Information**

CSA Standard: Yes  
cUL Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406

**Dimensions**

Depth U S: 0.833"  
Height U S: 3.281"  
Width U S: 1.322"

**Technical Information**

Amps: 20 Amp  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant