



## HEAVY-DUTY DECORATOR SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 250V, BROWN

26861 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Heavy-Duty Decorator Spec Grade Single Receptacle Back & Side Wire 20amp 250volt Brown



- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Single Receptacles  
Duty: Heavy Duty  
Special Features: Back,Side Wire  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: Yes

cULus: No  
cURus: No  
Federal Spec: Yes  
UL Listing No: No  
UN SPSC: 39121406  
UR: No

#### **DIMENSIONS**

Depth (US): 0.833"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 250V  
Volts (AC): 250  
Capacity: Single  
Grade Type: Federal Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

