



HEAVY-DUTY DECORATOR SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 250V, IVORY

268611 | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Decorator Spec Grade Single Receptacle Back & Side Wire 20amp 250volt Ivory



- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Single Receptacles
Duty: Heavy Duty
Special Features: Back,Side Wire
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
Federal Spec: Yes
UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.833"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A
Volts: 250V
Volts (AC): 250
Capacity: Single
Grade Type: Federal Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

