## **legrand**<sup>®</sup> designed to be better.

IG8200

# Isolated Ground Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 15A, 125V, Orange



IG8200

Isolated Ground Heavy-Duty Hospital Grade Duplex Receptacle, Back & Side Wire, 15amp 125volt, Orange. Also available in ivory and red. Add suffix 'i' for ivory, add suffix 'red' for red.



## features & benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.

### specifications

#### **General Info**

Color: orange Type: Receptacles Number Of Poles: 2 Number Of Wires: 3 Special Features: Isolated ground,back,side wire Style: Duplex

#### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42 CSA Standard: Yes Federal Spec: Yes Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406 UR: No

#### Dimensions

Depth U S: .922" Height U S: 3.281" Width U S: 1.322"

#### **Technical Information**

Amps: 15 Amp NEMA Configuration Number: 5-15R Volts: 125V Volts A C: 125 Capacity: Duplex Grade Type: Hospital,Federal Specification

#### **Buy American Act Compliance**

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant