La legrand[®] designed to be better.

Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Ivory



8301I

Heavy-Duty Hospital Grade Single Receptacle Back & Side Wire 20amp 125volt Ivory



features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: Ivory Type: Single, Receptacle Duty: Heavy Duty Special Features: Back,Side Wire

Listing Agencies/Third Party Information

CSA Standard: Yes cUL Standard: Yes cURus: No Federal Spec: Yes Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406 UR: No

Dimensions

Depth U S: 1.093" Height U S: 3.28" Width U S: 1.32"

Technical Information

Amps: 20 Amp Volts: 125V Volts A C: 125 Capacity: Single Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant