

Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 15A, 125V, White

PS5262W



Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt White

features & benefits



- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
- Eight back wire holes.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: white Type: Receptacles Duty: Heavy Duty

Special Features: Back, Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes Federal Spec: Yes

Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406

UR: No

Dimensions

Depth U S: .780" Height U S: 3.281" Width U S: 1.322"

Technical Information

Amps: 15 Amp Volts: 125V Volts A C: 125 Capacity: Duplex

Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant