



WIDE SLIDE SERIES FAN SPEED CONTROL, IVORY

94084I | Pass & Seymour

FEATURES & BENEFITS

1.5amp Slide Dehummer Fan Control, Ivory

• Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3- or 4-speed levels in slide, rotary, and dual styles with virtually no fan motor noise.

SPECIFICATIONS

GENERAL INFO

Color: Ivory

Product Series: Wide Slide

Type: Wide Side Number Of Poles: 1

Special Features: RFI Protected, De-Hummer

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes CUL Listing No: No

cULus: No cURus: No Federal Spec: No UL Listing No: Yes UN SPSC: 39121502 UR: No

DIMENSIONS

Depth (US): 1.469" Height (US): 4.25" Width (US): 1.688"

TECHNICAL INFORMATION

Amps: 1.5A Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant

