



## PLUGTAIL® DECORATOR SPEC GRADE RECEPTACLES, 15A, 125V, WHITE

PT26252W | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

PlugTail® Decorator Spec Grade Duplex Receptacle 15amp 125volt White

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Product Series: PlugTail  
Type: Receptacles  
Number Of Poles: 2  
Number Of Wires: 3  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E140596  
cULus: Yes  
cUL Standard: UL498  
Federal Spec: Yes  
UL Listing No: E140596  
UL Standard: UL498

UN SPSC: 39121406

## DIMENSIONS

Depth (US): .625"

Height (US): 3.281"

Width (US): 1.5"

## TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Federal Specification

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

