

---

## PLUGTAIL® ISOLATED GROUND SPEC GRADE RECEPTACLES, 15A, 125V, ORANGE



PTIG5262 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

PlugTail® Isolated Ground Spec Grade Duplex Receptacle 15amp 125volt Orange

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Orange

Product Series: PlugTail

Type: Receptacles

Special Features: Isolated Ground

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E140596

cULus: Yes

cUL Standard: UL498

Federal Spec: Yes

UL Listing No: E140596

UL Standard: UL498

UN SPSC: 39121406

#### DIMENSIONS

Depth (US): .625"  
Height (US): 3.281"  
Width (US): 1.5"

#### TECHNICAL INFORMATION

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: Yes  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Specification

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

