



PLUGTAIL® DECORATOR HOSPITAL GRADE RECEPTACLES, 20A, 125V, RED

PT26362HGRED | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Decorator Hospital Grade Duplex Receptacle 20amp 125volt Red

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Red
Product Series: PlugTail
Type: Receptacles
Number Of Poles: 2
Number Of Wires: 3
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E140596
cULus: Yes
cUL Standard: UL498
Federal Spec: Yes
UL Listing No: E140596
UL Standard: UL498

UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.625"

Height (US): 3.281"

Width (US): 1.5"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

NEMA Rating: Yes

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

