

LS Series Incandescent Slide Dimmer, Ivory

LS603PI



Incandescent Slide Dimmer, Preset 3way
600w, Ivory

features & benefits

- Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.
- Electromagnetic and radio-frequency interference protection built in.
- Sleek, sculpted contemporary design. No dirt-catching crevices.
- Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.
- Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.
- Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.
- Superior heat management.
- No derating on 600W units.
- Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

specifications

General Info

Color: Ivory
Product Series: LS
Type: Incandescent
Number Of Poles: 3-way

Listing Agencies/Third Party Information

CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPS C: 39121502
UR: No

Dimensions

Depth U S: 1.28"
Height U S: 4.19"
Width U S: 1.74"

Technical Information

Volts: 120V
Watts: 600

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No