

Hospital Grade MaxGrip M3 Plug, Gray

PS8115



Straight Blade Plug 2pole 3wire 15amp
125volt Hospital Grade



features & benefits

- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.

specifications

General Info

Color: Gray

Listing Agencies/Third Party Information

cULus: Yes
cURus: No
Federal Spec: Yes
Fed Spec Number: WC596
UL Standard: No
UN SPS C: 39121402

UR: No

Dimensions

Height U S: 1.83"

Width U S: 1.21"

Technical Information

Volts A C: 125

Grade Type: Hospital

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant