
HEAVY-DUTY GROUND CONTINUITY MONITORING (GCM) CONNECTOR, BLACK & WHITE

PSL515CGCM | [Pass & Seymour](#)



FEATURES & BENEFITS

TURNLOK GCM CONN 3W 15A 125V

- Integral indication of ground continuity and power status. Continuous monitoring enhances personnel safety and adds convenience.
- Dual, bright LED indicators with 360 degrees visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross. For 250V configurations: Hot to ground cross will be indicated by a green and red LED.
- NEMA configurations always visible for fast identification without disconnecting.
- Exclusive neoprene dust shield on devices seals cable entry. Optional weatherproof boots (sold separately).
- Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.
- Exclusive, rugged two-piece cord grip (15 Amp only) accepts a wide range of cord widths. Provides uniform pressure for superior retention of conductors.
- Recessed cord-grip screw reduces screwdriver slippage, improves safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.
- Color-coded terminal screws are backed-out for fast installation.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

SPECIFICATIONS

GENERAL INFO

Color: Black, White
Type: Connector, Ground Continuity Monitoring
Duty: Heavy Duty
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes
Federal Spec: Yes
UN SPSC: 39121403

DIMENSIONS

Diameter (US): 1.516"

Length (US): 2.598"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L5-15R

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

