



ISOLATED GROUND HEAVY-DUTY SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, IVORY

IG5262I | [Pass & Seymour](#)

FEATURES & BENEFITS

Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt Ivory



- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Receptacles
Number Of Poles: 2
Number Of Wires: 3
Special Features: Isolated ground,back,side wire
Style: Duplex

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 42

CSA Standard: Yes
Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 0.922"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Federal Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

