

Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond

IG5362LA



Isolated Ground Heavy-Duty Spec Grade
Duplex Receptacle Back & Side Wire
20amp 125volt Light Almond



features & benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: light almond
Type: Receptacles
Number Of Poles: 2
Number Of Wires: 3
Special Features: Isolated ground,back,side wire
Style: Duplex

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: 0.922"
Height U S: 3.281"
Width U S: 1.322"

Technical Information

Amps: 20 Amp
NEMA Configuration Number: 5-20R
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant