



TAMPER-RESISTANT HEAVY-DUTY
DECORATOR SPEC GRADE
RECEPTACLES, BACK & SIDE WIRE, 15A,
125V, LIGHT ALMOND

TR26262LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt Light Almond

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Type: Receptacles
Duty: Heavy Duty
Special Features: Tamper-Resistant,back,side wire
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes
cUL Standard: Yes
Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.833"

Height (US): 3.281"

Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Federal Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

