



## PLUGTAIL® SINGLE POLE 15 AMP TOGGLE SWITCH, BROWN

PT15AC1 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

PlugTail® Single Pole Toggle Switch, 15amp 120/277vac, Brown

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.
- Impact- and chemical- resistant cover.
- Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.
- One-piece nickel-plated mounting strap for superior corrosion resistance.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Auto-ground clip assures positive ground.
- Shallow design for easier installation.
- Heavy-duty bumpers for quiet, smooth operation.
- No exposed terminals create a finger-safe application before, during, and after installation.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Product Series: PlugTail  
Type: Toggle  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
cULus: Yes  
Federal Spec: Yes  
UL Standard: Yes  
UN SPSC: 39121507

#### DIMENSIONS

Depth (US): 1.073"  
Height (US): 3.281"  
Width (US): 1.320"

#### TECHNICAL INFORMATION

Amps: 15A  
Volts: 120/277VAC  
Volts (AC): 120/277  
Grade Type: Specification

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

