



PLUGTAIL® SPLIT CIRCUIT SPEC GRADE RECEPTACLES, 15A, 125V, BROWN

PT5262SC | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Split Circuit Spec Grade Duplex Receptacle 15amp 125volt, Brown

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Crimped and welded contacts.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Brown

Product Series: PlugTail

Type: Receptacles

Special Features: split circuit

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E140596

cULus: Yes

cUL Standard: UL498

Federal Spec: Yes

UL Listing No: E140596

UL Standard: UL498

UN SPSC: 39121406

DIMENSIONS

Depth (US): .625"
Height (US): 3.281"
Width (US): 1.5"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Federal Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

