



## PLUGTAIL® TAMPER-RESISTANT HOSPITAL GRADE RECEPTACLE, BACK & SIDE WIRE, 15A, 125V, WHITE

PTTR8200W | [Pass & Seymour](#)

### FEATURES & BENEFITS

PlugTail® Tamper-Resistant Hospital Grade Duplex Receptacle, Back & Side Wire, 15amp 125volt, White

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- **Dual mechanical shutter system** to help prevent insertion of foreign objects
- **.036 inch thick, brass, triple-wipe power contacts** for lasting retention.
- **Plated steel wrap strap design** for maximum durability and corrosion resistance.
- **No exposed terminals** create a finger safe application before, during, and after installation.
- **Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
- **Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.
- **Pre-stripped connector leads** fasten to conductors, easier than standard pigtails
- **Auto-ground clip** assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Receptacles

Special Features: PlugTail, Tamper-Resistant

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

CUL Listing No: E140596

cULus: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

## DIMENSIONS

Depth (US): 0.625"

Height (US): 3.281"

Width (US): 1.5"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Hospital

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

