



## TAMPER-RESISTANT FLOOR BOX ASSEMBLY - ONE GANG FOR WOOD SUB-FLOORS

FB1TRDRN | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Floor Box Assembly. #8 duplex opening. Two threaded screw plug, Includes 3232 15 amp, 125 volt tamper-resistant receptacle. Nickel.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Slater  
Component Type: Full Assemblies

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121308  
UR: No

#### DIMENSIONS

Depth (US): 4  
Length (US): 4.75  
Width (US): 3.25  
Volume: 20.5

#### TECHNICAL INFORMATION

Material: Nickel  
Floor Type: Wood

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

