

Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floors

FB1TRDRN



Tamper-Resistant Floor Box Assembly. #8 duplex opening. Two threaded screw plug, Includes 3232 15 amp, 125 volt tamper-resistant receptacle. Nickel.

features & benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.



specifications

General Info

Product Series: Slater
Component Type: Full Assemblies

Listing Agencies/Third Party Information

CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPS C: 39121308

UR: No

Dimensions

Depth U S: 4.0
Length U S: 4.75
Volume: 20.5
Width U S: 3.25

Technical Information

Material: Nickel
Floor Type: Wood

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant