



20A SPEC-GRADE TAMPER-RESISTANT RECEPTACLE, LIGHT ALMOND

TR26352RLA | [Pass & Seymour](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Part of the all-new radiant® collection.
- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- High impact-resistant nylon face for durability.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- .032-inch thick brass triple-wiper power contacts for reliable plug retention.
- Backed-out tri-drive steel terminal screws for faster installation.
- Corrosion-resistant, plated steel strap.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Number Of Poles: 2

Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

UL Listing No: UL498

UN SPSC: 39121406

CONSTRUCTION INFORMATION

Component 4: 78500705603

DIMENSIONS

Depth (US): 0.65"

Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

