# $\mathbf{NEXTSPEED}^{\mathbb{R}}$

#### **Jacks**

# **Xcelerator Category 6 Jack**

# HUBBELL

#### **Features**

- Third Party Verified Category 6 Component Compliant
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Mating Cycles Exceed Industry Standard by Four Times
- Bulk Packaging Reduces Excess Waste on the Job

### **Ordering Information**

Description Color **UPC Number** Catalog No. HXJ6W **NEXTSPEED Xcelerator** 662620825281 White Category 6 Component Jack, 1

# Listings

ANSI/TIA/EIA-568-C.2 Category 6 component ISO 11801/60603-7-41 Category 6 component Mechanical: Verified to TIA-568-C.2 UL Listed 1863 Mechanical TIA-568-C.2 **CSA Certified** RoHS Compliant

# **Specifications**

Nose Contact Beryllium copper with precious metal plating over nickel under plating Phosphor bronze with 100 micro-inch tin **IDC** Contact lead 60/40 plating over nickel under plating High impact thermoplastic (UL 94 V-0) Housing Stuffer Cap Lexan® (UL 94 V-0)

#### **Performance**

#### **Electrical**

4+Gbs capacity within the bandwidth of 1-250MHz (channel) Center balanced to Category 6 plug specifications Positive PSACR beyond 300 MHz (channel) Qualified to 150% of 802.3bt PoE Current Level

#### **General Information**

100% factory tested Backward compatible to lower installed Categories Icon Compatible Supporting 606-B requirements

#### Mechanical


Contact performance confirmed over the full range of ISO/FCC compliant plug

IDC Contact Termination: 10x Keystone Latching Force: 25 lbs.

# **Applications**

IEEE 802.3ab 1000GBASE-T IEEE 802.3bt 4PPoE Power over Ethernet TIA TSB-155 10GbE Over 55 Meters





# **Complementary Products**

TX4P 1-Punch Tool HC6W03 Category 6 Patch Cord HXJDC25 **Dust Cover Termination Puck** HXTP25 Category 6 Cable C6SPB

#### Online Resources

eCatalog

