NEXTSPEED® Jacks

HUBBELL

Xcelerator Category 6 Jack

Features

- Third Party Verified Category 6 Component Compliant
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Mating Cycles Exceed Industry Standard by Four Times
- Bulk Packaging Reduces Excess Waste on the Job

Ordering Information

Description Color **UPC** Catalog No. **NEXTSPEED Xcelerator** Black HXJ6BK 662620825328 Category 6 Component Jack, 1 Jack

Listings

ANSI/TIA/EIA-568-C.2 Category 6 component ISO 11801/60603-7-41 Category 6 component Mechanical: Verified to TIA-568-C.2 UL Listed 1863 Mechanical TIA-568-C.2 **CSA Certified RoHS Compliant**

Specifications

Nose Contact Beryllium copper with precious metal plating over nickel under plating **IDC Contact** Phosphor bronze with 100 micro-inch tin lead 60/40 plating over nickel under plating High impact thermoplastic (UL 94 V-0) Housing Lexan® (UL 94 V-0) Stuffer Cap

Performance

Electrical

Center balanced to Category 6 plug specifications Positive PSACR beyond 300 MHz (channel) 4+Gbs capacity within the bandwidth of 1-250MHz (channel) Qualified to 150% of 802.3bt PoE Current Level

General Information

Backward compatible to lower installed Categories Icon Compatible Supporting 606-B requirements 100% factory tested

Mechanical


Nose Contact Mating Cycles: 2000 IDC Contact Termination: 10x Keystone Latching Force: 25 lbs.

Contact performance confirmed over the full range of ISO/FCC compliant plug

Applications

IEEE 802.3ab 1000GBASE-T IEEE 802.3bt 4PPoE Power over Ethernet TIA TSB-155 10GbE Over 55 Meters





Accessories

1-Punch Tool TX4P Category 6 Patch Cord HC6BK03 **Dust Cover** HXJDC25 **Termination Puck** HXTP25 C6SPB Category 6 Cable

Online Resources

Customer Use Drawing eCatalog

