APPLICATIONS

 General and accent flood lighting where short burning hours are planned. Instant on/off

SPECIFICATIONS

- 150 to 500 watt capability
- Die cast aluminum construction for long life
- · Single screw door closure for easy installation
- · Tempered glass lens protects lamp
- 1/2" cast swivel knuckle fits standard boxes and covers
- Wide, uniform beam for even illumination
- 120 volt lamps are included
- Units offered in dark bronze or white powder paint finish

LISTINGS

• Listed to UL1598 for use in wet locations

0500X В C C В D Q150X 57/16" 37/8" 51/2" 4" 100 mm 138 mm 98 mm 139 mm Q500X 723/32" 813/16" 35/8" 92 mm 196 mm 227 mm

0150X

CERTIFICATIONS/LISTINGS





ORDERING INFORMATION

Catalog Number	Wattage/Voltage	Color	Photometry NEMA/IES H° x V°	Weight Ibs. (kg)	EPA ft² (m²)
Lamp Included					
Q-150-W	150w/120V	White	6(124°) x 6(124°)	1.4 (0.6)	.14 (.01)
Q-500-B	500w/120V	Bronze	6(100°) x 5(86°)	2.6 (1.2)	.6 (.05)

PHOTOMETRIC REPORTS

Catalog Number	Report #		
Q150X	HP06551A		
Q500X	HP10062.IES		

