

JUNO®

UNDERCABINET LIGHTING

LED SWITCHABLE WHITE, DIMMABLE

UCES

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____



PRODUCT DESCRIPTION

Provides task or accent lighting in commercial, retail, hospitality and residential applications. Ideal for use under and over cabinets, display cases, task lighting, office lighting, coves and utility/work areas.

PRODUCT SPECIFICATIONS

LEDs Long-life LEDs, coupled with a high-efficiency driver, provide extended service life • Fixture is rated to deliver L70 performance at 50,000 hours and operates at 120 volts, 60Hz • Minimum starting temp -20F • Can direct-wire through rear access plate/knockout by utilizing the included Romex connector • Works with most standard incandescent dimmers (see list of approved dimmers).

Housing Low profile design • Can be direct wired • Rugged post-painted low-profile steel housing with white finish • Acrylic white diffuser provides soft widespread illumination with zip-lock design for easy installation, cleaning, and superior retention.

Diffuser Lightly frosted, acrylic diffuser for maximum light transmission and uniform light distribution.

Labels UL listed to US and Canadian safety standards • ENERGY STAR® certified product and Title 24 qualified. Listed for damp locations.

Warranty 5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25 °C.

Specifications subject to change without notice.

INSTALLATION

All mounting hardware included.



ENGINEERING DATA

	12"			18"			24"			36"		
	2700K	3000K	3500K	2700K	3000K	3500K	2700K	3000K	3500K	2700K	3000K	3500K
Lumens	454	482	492	595	621	646	788	825	853	1169	1222	1161
Wattage	6.5			8.4			10.8			16.4		
Lumens/Watt	70	74	76	70	74	76	72	77	79	71	75	76
Length	12 (30.5)			18 (45.7)			24 (61)			36 (91.4)		
Width	2.55 (6.5)			2.55 (6.5)			2.55 (6.5)			2.55 (6.5)		
Height	1.07 (2.7)			1.07 (2.7)			1.07 (2.7)			1.07 (2.7)		
Weight	1 (.45)			1 (.45)			1 (.45)			1 (.45)		

All dimensions are inches (centimeters) unless otherwise indicated. Weights are pounds (kilograms).

ORDERING INFORMATION

Example: UCES 12IN SWW6 90CRI WH

Series	Length	CCT	CRI	Finish
UCES Economy LED Undercabinet	12IN 12 inch	SWW6 2700K, 3000K, 3500K	90CRI 90 CRI	WH White
	18IN 18 inch			
	24IN 24 inch			
	36IN 36 inch			

Dimmer Compatibility

Lutron	Eaton
Skylark SCL-153P	HALO SALO6P
Toggle TGCL-153P	
Lumeo LECL-153P	
Maestro MACL-153M	
Caseta PD-6WCL	
DVCL-153P	
D-603P	
SCT-603P	
DVELV-300P	
DV-603P	
S-600P	