

# Hangers and Straps

## All-Round Strapping



Handy Dispenser Carton



1/2" - 22GA | 3/4" - 24GA | 3/4" - 20GA

- 1/2" straps have 3/16" bolt holes
- 3/4" straps have large holes for 1/4" bolts and small 1/8" holes for screw or nails

### GALVANIZED STEEL

Description	Max Load lbs	Part Number	Box/Mstr
1/2" x 25' - 24 Gauge	95	9049	20
3/4" x 10' - 24 Gauge	130	9043	40
3/4" x 25' - 24 Gauge	130	9047	20
3/4" x 100' - 24 Gauge	130	9048	5
3/4" x 25' - 20 Gauge	210	9040	20
3/4" x 100' - 20 Gauge	210	9045	5

### NYLON COATED (Galvanized Steel)

Description	Max Load lbs	Part Number	Box/Mstr
1/2" x 10' - 24 Gauge	110	9090	40
1/2" x 25' - 24 Gauge	110	9080	20
3/4" x 25' - 24 Gauge	130	9085	20

### SOLID COPPER

Description	Max Load lbs	Part Number	Box/Mstr
1/2" x 10' - 22 Gauge	60	9053	40
1/2" x 25' - 22 Gauge	60	9050	20
3/4" x 25' - 24 Gauge	55	9060	20
3/4" x 25' - 20 Gauge	130	9070	20

### STEEL

Description	Max Load lbs	Part Number	Box/Mstr
1/2" x 10' - 22 Gauge	110	9015	40
1/2" x 25' - 22 Gauge	110	9010	20
3/4" x 10' - 24 Gauge	130	9021	40
3/4" x 25' - 24 Gauge	130	9020	20
3/4" x 100' - 24 Gauge	130	9025	5
3/4" x 25' - 20 Gauge	210	9030	20
3/4" x 100' - 20 Gauge	210	9035	5

\* INDICATED MAXIMUM LOAD IS APPROXIMATELY 1/3 OF BREAKING LOAD FOR SINGLE STRAPS.

ANG = Angle, STR = Straight, PL = Plated, RB = Rough Brass