

J Type Double Ended



T3 - 79 mm



T3 - 119 mm



T3 - 256 mm

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
T3 - 79 mm								
68200	H60T3/79mm/CL/2M/R7S/130V/STD	60	R7s	130	800	2 000	Clear	12/120
57225	H75T3/79mm/2M/R7S/120V/STD	75	R7s	120	750	2 000	Clear	12/480
55047	H75T3/79mm/CL/2M/R7S/130V/JPN/STD	75	R7s	130	1 150	2 000	Clear	12/480
57361	H100T3/79mm/2M/R7S/120V/STD	100	R7s	120	1 300	2 000	Clear	12/120
51043	H100T3/79mm/2M/R7S/130V/STD	100	R7s	130	1 300	2 000	Clear	12/120
57224	H150T3/79mm/2M/R7S/120V/STD	150	R7s	120	2 400	2 000	Clear	12/120
51075	H150T3/79mm/2M/R7S/130V/STD	150	R7s	130	2 400	2 000	Clear	12/120
51120	H200T3/79mm/2M/R7S/130V/STD	200	R7s	130	3 400	2 000	Clear	12/120
T3 - 119 mm								
51086	H100T3/119mm/2M/R7S/130V/STD	100	R7s	130	1 300	2 000	Clear	12/120
50903	H150T3/119mm/2M/R7S/130V/STD	150	R7s	130	1 800	2 000	Clear	12/120
51044	H200T3/119mm/2M/R7S/130V/STD	200	R7s	130	3 400	2 000	Clear	12/120
51078	H300T3/119mm/CL/2M/R7S/120V/STD	300	R7s	120	5 950	2 000	Clear	12/120
51041	H300T3/119mm/CL/2M/R7S/130V/STD	300	R7s	130	5 950	2 000	Clear	12/120
51076	H500T3/119mm/CL/2M/R7S/120V/STD	500	R7s	120	10 500	2 000	Clear	12/120
51077	H500T3/119mm/CL/2M/R7S/130V/STD	500	R7s	130	10 500	2 000	Clear	12/120
T3 - 190 mm								
51046	H1000T3/190mm/CL/2M/R7S/130V/STD	1 000	R7s	130	21 000	2 000	Clear	12/120
T3 - High Voltage								
59261	H300QT3/119mm/CL/2M/220V/STD	300	R7s	220	33 000	2 000	Clear	12/120
51047	H1000T3/190mm/CL/2M/R7S/240V/STD	1 000	R7s	240	21 000	2 000	Clear	12/120
51085	H1000T3/256mm/CL/2M/R7S/240V/STD	1 000	R7s	240	21 000	2 000	Clear	12/120
59262	H1500QT3/256mm/CL/2M/R7S/208V/STD	1 500	R7s	208	33 000	2 000	Clear	12/120
51049	H1500T3/256mm/CL/2M/R7S/240V/STD	1 500	R7s	240	26 400	2 000	Clear	12/120
59260	H1500QT3/256mm/CL/2M/277V/STD	1 500	R7s	277	33 000	2 000	Clear	12/120
T3 - Low Voltage								
55088	H150T3/79mm/2M/R7S/12V/STD	150	R7s	12	2 900	2 000	Clear	10/100
10318	H300T3/119mm/CL/2M/R7S/24V/STD	300	R7s	24	5 400	2 000	Clear	10/100
10319	H300T3/119mm/CL/2M/R7S/32V/STD	300	R7s	32	5 400	2 000	Clear	10/100
T3 - Infrared								
55077	H375T3/221mm/CL/IR/5M/R7S/120V/STD	375	R7s	120	N/A	5 000	Clear	1/84
55070	H500T3/221MM/CL/IR/5M/R7S/120V/STD	500	R7s	120	N/A	5 000	Clear	1/25
55072	H1000T3/351MM/CL/IR/5M/ML/240V/STD	1 000	Metal Leads	240	N/A	5 000	Clear	1/25
55074	H1600T3/503MM/CL/IR/5M/ML/240V/STD	1 600	Metal Leads	240	N/A	5 000	Clear	1/25
55076	H3800T3/1062MM/CL/IR/5M/ML/570V/STD	3 800	Metal Leads	570	N/A	5 000	Clear	1/25

