ALUMINUM MOUNTING CHANNEL

4' / 8' MINI-DEEP FORMAT

PRODUCT OVERVIEW

GM Lighting's LED-CHL-XD-MD channel accepts all low voltage GM Lighting LED tape. Available in 48" and 96" lengths, these mounting channels are the perfect vessel that not only insures an architectural quality installation, but also minimize diode imaging due to the frosted lens that is included with each channel.

FEATURES

- · Available in 4ft (48in) and 8ft (96in)
- Silver Anodized, Black Anodized, White Powder Coated
- Includes 2 mounting clips and screws with 4ft,
 4 mounting clips and screws with 8ft
- Includes acrylic frosted lens
- · End caps sold separately
- Available with or without flange (see LED-CHL-XD-MD-F spec sheet for flange option ordering information)
- For LTR Series Tape LTR-P, LTR-S and LTR-E
- · Custom lengths available consult factory
- Dry location only

Note: For Vision120, use V120-CHL channels. This channel will not fit the LTR-P-WP and LTR-S-24V-RGBW connectors.

SPECIFICATIONS

ELECTRICAL

• Fits 12V/24V LEDtask LED tape

WARRANTY

• 5-year warranty

ORDERING INFORMATION

Model	Туре	Format	Length	Color
LED-CHL	XD	MD	Blank (4 ft.)	Blank (Silver Anodized)
			8 (8 ft.)	WH (White Powder Coated)
				B (Black Anodized)

Accessories

Model	Description	
LED-CHL-XD-MD-AMC	(2) Adjustable mounting brackets (stainless steel)	
LED-CHL-XD-MD-EC	(2) End caps - one solid, one with wiring hole	
LED-CHL-XD-MD-ECB	(2) Black End caps - one solid, one with wiring hole	
LED-CHL-XD-MD-MC	(2) Mounting clips (stainless steel)	



Project Name	Туре
Catalog #	Date



Example: LED -CHL-XD-MD-WH


ALUMINUM MOUNTING CHANNEL



4' / 8' MINI-DEEP FORMAT

Model	Dimensions	Connectors	Compatibility	Finish
LED-CHL-XD-MD			LTR-P (except WP),	Blank (Silver Anodized)
LED-CHL-XD-MD-8				
LED-CHL-XD-MD-WH	L48"or 96" x W.75" x	Sure-Tite and EZ	LTR-S (except RGBW),	WILL (White Develor Control)
LED-CHL-XD-MD-8-WH	D.62"	Connectors	LTR-E Series Dry Location	WH (White Powder Coated)
LED-CHL-XD-MD-B				D (Dia ala Anna dia a d)
LED-CHL-XD-MD-8-B				B (Black Anodized)

DIAGRAM



DIMENSIONS

