SATCO' NUVO



S11288

10W/LED/STRING/RGBW/SF

GENERAL SPECIFICATIONS

Shape: Wattage: Lumen Output: Color Temperature: Base: S14 10W 260LL 2700K/5000K 4-Pin



TECHNICAL SPECIFICATIONS

Wattage:	10W
Volts:	120V
Shape:	S14
Base:	4-Pin
Finish:	Black
Hours Rated:	15000H
Color Temperature:	2700K/5000K

DIMENSIONS			
/eight:	3.86		

CRI:	80CRI
Lumen Output:	260L
Dimmable:	Yes-Dimmable
Dimming Function:	Only with Starfish App; Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Power Factor:	0.5
Operating Temp:	-20C (-4F) to a maximum of +45C (+113F)
Safety Listing:	cETLus
Technology:	LED
Material:	Plastic

LISTINGS				
Safety Listing:	cETLus			
Location Rating:	Wet			
Energy Star:	No			
CA Prop 65:	Lead			
IP Rating:	IP65			
RoHS Compliant:	Yes			

PACKAGING

Each UPC:	045923112881	Inner UPC:	20045923112885	Case UPC:	10045923112888
Each Quantity:	1	Inner Quantity:	0	Case Quantity:	4
Each Dimensions:	13.19 x 4.33 x 13.19"	Inner Dimensions:	0.00 x 0.00 x 0.00"	Case Dimensions:	18.31 x 13.78 x 13.98"

110 Heartland Blvd.		
Brentwood, NY 11717		
PH 631-243-2022		
FX 631-243-2027		

Distribution Centers New York, Florida, Texas, Washington, California, Puerto Rico

National Toll-Free 800-43-SATCO (800-437-2826) www.satco.com Copyright 2022 Satco Products, Inc. All Rights Reserved May 22, 2022