

# Eaton CE15GNS3AB

Catalog number: CE15GNS3AB

Eaton XT IEC contactor, 37A, 110-120 Vac, 50-60 Hz, 1NO, 37A, Frame G, 90 mm, 50-60 Hz, 3 hp, Side, Three-pole, Non-reversing, No overload relay, Freedom, Contactor



## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

CE15GNS3AB

### UPC

782113007878

### Product Length/Depth

4.22 in

### Product Height

4.27 in

### Product Width

2.56 in

### Product Weight

2.12 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

ISO 9000 DIN VDE 0600

### Certifications

UL Listed IEC Rated CSA Certified

### Catalog Notes

No enclosure

## defaultTaxonomyAttributeLabel

### Frame size

90 mm

### Contact configuration

1 NO

### Coil voltage

110-120 Vac, 50-60 Hz

### Series

Freedom

### Type

Contact

### Relay

No overload relay

### HP rating - max

3 hp

### Continuous ampere rating

37 A

### Frequency rating

50-60 Hz

### Operation

Non-reversing

### Mounting method

Side

### Amperage Rating

37A

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

[Motor Starters and Contactors — Low Voltage Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - CE15GNS3AB](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)