

# Eaton C25DNJ350B

Catalog number: C25DNJ350B

Eaton definite purpose contactor, Mounting plate, Quick, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Three-pole, E1, Box lugs (posidrive setscrew), Non-reversing



## General specifications

### Product Name

Eaton definite purpose contactor

### Catalog Number

C25DNJ350B

### UPC

782116300730

### Product Length/Depth

3.35 in

### Product Height

3.75 in

### Product Width

2.4 in

### Product Weight

1.3 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

RoHS Compliant CE Marked

### Certifications

CSA Certified UL Listed file E1491 (Guide Number NLDX2)

## defaultTaxonomyAttributeLabel

### Frame size

15-50 A, two-pole and three-pole

### Accessories

Mounting plate

### Coil voltage

50/60 Hz

### Series

E1

### Type

Non-reversing

### Auxiliary contacts

Quick connect (vertical in-line)

### Model

Contactor

### Connection

Quick

### Enclosure

Open with metal mounting plate

### Terminals

Box lugs (posidrive setscrew)

### Coil

208-240 Vac

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25DNJ3 3D Inventor](#)

[C25DNJ3 AutoCAD 2D Footprint \(mm\)](#)

[C25DNJ3 3D Model Xchange](#)

[C25DNJ3 AutoCAD 2D Footprint](#)

[C25DNJ3 2D PDF](#)

[C25DNJ3 2D Drawing Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25DNJ350B](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)