

Eaton BR290

Catalog number: BR290

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 90 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #8-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters

General specifications



Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR290
	UPC
	786676363204
Product Length/Depth	Product Height
2 in	2.5 in
Product Width	Product Weight
2.9 in	.7 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

Physical Attributes

Circuit breaker type

BR

Mounting Method

Plug-on

Number of poles

Two-pole

Type

Type BR 1-Inch plug-on circuit breaker

Wire size

#8-1/0 AWG Cu/Al

Performance Ratings

Amperage Rating

90 A

Interrupt rating

10 kAIC

Trip Type

Common breaker trip

Voltage rating

120/240 V

Miscellaneous

Main circuit breaker

BR

Quantity

28

Special features

Used with Type BR Loadcenters

Used with

Type BR Loadcenters

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR290](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)