Eaton PSG120E

Catalog number: PSG120E

Power Supply, 120W, Single-phase, 100-240V input voltage, 24 Vdc \pm 2% output voltage, 1.4A input current, 5A output current, less than 80A inrush current, 47-63 Hz, 85-264V, 120-375 Vdc, Aluminum enclosure, Heavyduty screw terminals

General specifications

Product Name

Catalog Number

Eaton PSG general purpose power

PSG120E

supply

UPC

786685215440

Product Length/Depth

Product Height

4.76 in

4.53 in

Product Width

Product Weight

1.97 in

.81 lb

Warranty

Compliances

Eaton Selling Policy 25-000, one (1) year German Safety CE Marked RoHS

from the date of installation of the

Compliant

Product or eighteen (18) months from the

Certifications

date of shipment of the Product,

whichever occurs first.

UL 508 cULus/UL 60950-1 CSA

Certified IEC Rated cUL Certified EN

Listed

Catalog Notes

Ratings for single-phase are at 115V. 0

Hz at DC input.





defaultTaxonomyAttributeLabel

Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection, finger-safe cover

Phase

Single-phase

Operating temperature - min

-20 °C

Input voltage

100-240 Vac

Output voltage

24 V

Enclosure material

Aluminum

Series

PSG

Power consumption

120 W

Operating temperature - max

75 °C

Frequency rating

47-63 Hz

Terminals

Heavy-duty screw

Voltage rating

85-264 Vac, 100-375 Vdc

Rated operational current

7.5 A surge

Less than 80 A inrush

5 A output

1.4 A input

Resources

Brochures

Eaton's PSG Series Power Supplies

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Drawings

PSG120E AutoCAD 2D Footprint (mm)

Installation instructions

Installation Instructions for PSG120E Power Supply

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - PSG120E

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2022 Eaton

All Rights Reserved

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia