

Eaton S611F414N3S

Catalog number: S611F414N3S

Reduced voltage motor solid state starters, Standard, Rating: 150 hp at 208V, 150 hp at 240V, 350 hp at 480V, 450 hp at 600V, 414A, Three-phase, F-frame



General specifications

Product Name

Eaton S811+/S801+ soft starter

Catalog Number

S611F414N3S

UPC

786685480398

Product Length/Depth

29.69 in

Product Height

9.5 in

Product Width

17.56 in

Product Weight

86 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

IEC 60947-2 CSA Std. C22.2 No.235

UL 1077

Frame size

F

Type

Standard

HP rating - max

150 hp at 208V, 150 hp at 240V, 350 hp at 480V, 450 hp at 600V

Phase

Three-phase

Amperage Rating

414A

Application notes

[S8x1 adjustment - Switching from S801+ to S811+](#)

Brochures

[S611 Soft Starters](#)

Catalogs

[Product Range Catalog Drives Engineering](#)[Eaton's Volume 6—Solid-State Motor Control](#)

Drawings

[S611F 3D Model Xchange](#)[S611F AutoCAD 2D Footprint](#)[S611F 2D Drawing Xchange](#)[S611F AutoCAD 2D Footprint \(mm\)](#)[S611 Frame E/F Soft Starter](#)

Installation instructions

[S611 Soft Starter Quick Start Installation Guide](#)

Multimedia

[Soft starter DS7 up to 200 A](#)[Soft Starter DS7 up to 32 A](#)[Soft Starter Product Family Overview](#)

Specifications and datasheets

[Eaton Specification Sheet - S611F414N3S](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)