

Eaton S811+V72N3S

Catalog number: S811+V72N3S

Eaton S811+ soft starter, Soft Starter, 290MM, 720 A, with OPT Inside the Delta

General specifications



Product Name
Eaton S811+ soft starter

Catalog Number
S811+V72N3S

UPC
78668559162

Product Length/Depth
23.5 in

Product Height
11.5 in

Product Width
16.5 in

Product Weight
108 lb

Certifications
Contact Manufacturer

Frame size

V

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

Type

Standard

Rating

257 kW at 230 V, 475 kW at 380-400 V, 500 kW at 440 V

Amperage Rating

850A

Application notes

S8xL adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - S811+V72N3S

Drawings

Type S811+ Soft Starter - V-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

Multimedia

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+V72N3S



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia