

# Eaton E50DS2

Catalog number: E50DS2

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, Side pushbutton, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 201°F (-10° to 94°C), E50 Heavy Duty Factory Sealed 6P+,Adjustable spring return

## General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50DS2
	UPC
	782113290638
Product Length/Depth	Product Height
1.05 in	2.79 in
Product Width	Product Weight
1.54 in	.11 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Recognized CSA Certified	

**Enclosure material**

Die cast zinc

**Series**

E50 heavy duty factory sealed 6P+

**Operating temperature - min**

14 °F

**Operating temperature - max**

201 °F

**Environmental rating**

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

**Actuator**

Side pushbutton

**Catalogs**

[Eaton's Volume 8—Sensing Solutions](#)

**Specifications and datasheets**

[Eaton Specification Sheet - E50DS2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)