

Eaton SVX060A1-4A1N1

Catalog number: SVX060A1-4A1N1

Eaton SVX adjustable frequency drive, Independent Drives, 60 hp, NEMA Type 1/IP21, 480 V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX060A1-4A1N1
UPC	Product Length/Depth
782116011568	10.1 in
Product Height	Product Width
16 in	9.3 in
Product Weight	Warranty
77.2 lb	2 year
Compliances	Certifications
Contact Manufacturer	EN 61800-3 Level H UL 508C IEC 61800-2

Frame size

7

Modification

Standard boards

Input

Three-phase

EMC H

Brake chopper

No brake chopper

Horsepower

60 hp

Keypad

Alphanumeric

Rating

NEMA 1, IP21

Software

Standard

Voltage rating

480 V

Application notes[SPI - Variable frequency drives with a common DC bus](#)[Connecting drives to generator supplies](#)[Electromagnetic compatibility \(EMC\)](#)**Brochures**[SVX9000 Adjustable Frequency Drives Brochure](#)[SVX9000 Adjustable Frequency Drives Product Aid](#)**Catalogs**[Product Datasheet - SVX060A1-4A1N1](#)[Product Range Catalog Drives Engineering](#)[Eaton's Volume 6—Solid-State Motor Control](#)**Drawings**[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)[SVX_\(FR7\) 2D Drawing Xchange](#)[SVX_\(FR7\) AutoCAD 2D Footprint](#)[SVX_\(FR7\) 3D Model Xchange](#)[SVX_\(FR7\) 2D PDF](#)[SVX_\(FR7\) 3D Inventor](#)[SVX_\(FR7\) AutoCAD 2D Footprint \(mm\)](#)**Installation instructions**[9000X AFD User Manual](#)**Specifications and datasheets**[Eaton Specification Sheet - SVX060A1-4A1N1](#)