

Eaton XBUT4

Catalog number: XBUT4

Eaton XB IEC terminal block, 6.2 mm Screw connection single level-through-feed, Gray, 10 AWG/4 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #26-10 AWG, EN #26-10 AWG, UL #26-10 AWG wire, IEC 41A, EN 30,38A, UL 30A



General specifications

Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT4
UPC	Product Length/Depth
782116894284	1.85 in
Product Height	Product Width
2 in	.15 in
Product Weight	Warranty
.01 lb	1 year
Certifications	
UL Listed CSA Certified	

defaultTaxonomyAttributeLabel

Type

IEC-XB Series

Voltage rating

IEC 800V, EN 700V, UL 600V

Amperage Rating

41A (IEC), 30A (EN), 38A (EN), 30A (UL)

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)