

Eaton SVX030A1-5A4B1

Catalog number: SVX030A1-5A4B1

Eaton SVX adjustable frequency drive, 30HP, NEMA Type 1/IP21, 575V, FR7, Three-phase, EMC L, Standard Software, A/N keypad, Internal brake chopper, Standard boards



General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX030A1-5A4B1
UPC	Product Length/Depth
782116929238	10.1 in
Product Height	Product Width
24.8 in	9.3 in
Product Weight	Warranty
77.2 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2 EN 61800-3 Level H UL 508C

defaultTaxonomyAttributeLabel

Frame size

7

Modification

Standard boards

Input

EMC L

Three-phase

Brake chopper

Brake chopper

Horsepower

30 hp

Keypad

Alphanumeric

Rating

NEMA 1, IP21

Software

Standard

Voltage rating

575 V

Resources

Application notes

[Connecting drives to generator supplies](#)

[SPL - Variable frequency drives with a common DC bus](#)

[Electromagnetic compatibility \(EMC\)](#)

Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Range Catalog Drives Engineering](#)

[Product Datasheet - SVX030A1-5A4B1](#)

Drawings

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

Installation instructions

[9000X AFD User Manual](#)

Specifications and datasheets

[Eaton Specification Sheet - SVX030A1-5A4B1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)