

Eaton SVX050A1-5A4B1

Catalog number: SVX050A1-5A4B1

Eaton SVX adjustable frequency drive, 50HP, NEMA Type 1/IP21, 575V, FR8, Three-phase, EMC L, Standard Software, A/N keypad, Internal brake chopper, Standard boards



General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX050A1-5A4B1
UPC	Product Length/Depth
782116929252	13.5 in
Product Height	Product Width
30.1 in	11.5 in
Product Weight	Warranty
127 lb	2 year
Compliances	Certifications
Contact Manufacturer	EN 61800-3 Level H UL 508C IEC 61800-2

defaultTaxonomyAttributeLabel

Frame size

8

Modification

Standard boards

Input

Three-phase

EMC L

Brake chopper

Brake chopper

Horsepower

50 hp

Keypad

Alphanumeric

Rating

NEMA 1, IP21

Software

Standard

Voltage rating

575 V

Resources

Application notes

[SPI - Variable frequency drives with a common DC bus](#)

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

Catalogs

[Product Range Catalog Drives Engineering](#)

[Product Datasheet - SVX050A1-5A4B1](#)

[Eaton's Volume 6—Solid-State Motor Control](#)

Drawings

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

Installation instructions

[9000X AFD User Manual](#)

Specifications and datasheets

[Eaton Specification Sheet - SVX050A1-5A4B1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)