

Eaton XBUT10BU

Catalog number: XBUT10BU

Eaton XB IEC terminal block, 10.2 mm Screw connection single level-through-feed, Blue, 12 AWG/2.5 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #26-12 AWG, EN #26-12 AWG, UL #26-12 AWG wire, IEC 32A, EN 22,28A, UL 20A



General specifications

Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT10BU
UPC	Product Length/Depth
782116904983	1.85 in
Product Height	Product Width
2.17 in	.4 in
Product Weight	Warranty
.04 lb	1 year

Certifications

UL Listed CSA Certified

defaultTaxonomyAttributeLabel

Type

IEC-XB Series

Voltage rating

IEC 800V, EN 700V, UL 600V

Amperage Rating

32A (IEC), 22A (EN), 28A (EN), 20A (UL)

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[XBUT10 AutoCAD 2D Footprint \(mm\)](#)

[XBUT10 3D Model Xchange](#)

[XBUT10 2D Drawing Xchange](#)

[XBUT10 AutoCAD 2D Footprint](#)

[XBUT10 2D PDF](#)

[XBUT10 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT10BU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)