

Eaton XTMC9A10E

Catalog number: XTMC9A10E

Eaton XT IEC mini contactor, 8.80A, 208 Vac, 60 Hz, 1NO, 20A, 45 mm mini, 60 Hz, 0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing mini contactor



General specifications

Product Name	Catalog Number
Eaton XT IEC mini contactor	XTMC9A10E
EAN	Product Length/Depth
4015082102562	2.5 in
Product Height	Product Width
2 in	2.5 in
Product Weight	Compliances
.5 lb	RoHS Compliant CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Contact configuration

1 NO

Coil voltage

208 Vac, 60 Hz

Series

XT IEC

Type

Full voltage non-reversing mini contactor

HP rating - max

0.5, 1, 1.5/ 2, 3, 5, 5 hp (1/3PH @ 115,200,230/200,230,460,575 V)

Continuous ampere rating

20 A

Frequency rating

60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

8.80A

Number Of Poles

Three-pole

Resources

Brochures

[XT IEC power control 580–2600A vacuum contactors](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTMC 2D Drawing Xchange](#)

[XTMC AutoCAD 2D Footprint](#)

[XTMC 2D PDF](#)

[XTMC 3D Model Xchange](#)

[XTMC 3D Inventor](#)

[XTMC AutoCAD 2D Footprint \(mm\)](#)

Multimedia

[Contactors Explained](#)

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Eaton Specification Sheet - XTMC9A10E](#)

[Global Data Sheet - XTMC9A10E](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)