

Eaton XTCE095F00A

Catalog number: XTCE095F00A

Eaton XT IEC contactor, 95A, 110 Vac 50 Hz, 120 Vac 60 Hz, ONO-ONC, 95A, Frame F, 90 mm, 50-60 Hz, 7.5, 15, 15/ 25, 40, 75, 100 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE095F00A
EAN	Product Length/Depth
4015082394776	7 in
Product Height	Product Width
4 in	7 in
Product Weight	Compliances
6 lb	CE Marked RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

90 mm

Contact configuration

0 NO, 0 NC

Coil voltage

110-120 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

7.5, 15, 15/ 25, 40, 75, 100 hp (1/3PH
@115,200,230/200,230,460,575 V)

Continuous ampere rating

95 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

95A

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_F 2D PDF](#)

[XTCE_F 2D Drawing Xchange](#)

[XTCE_F 3D Inventor](#)

[XTCE_F AutoCAD 2D Footprint](#)

[XTCE_F 3D Model Xchange](#)

Specifications and datasheets

[Global Data Sheet - XTCE095F00A](#)

[Eaton Specification Sheet - XTCE095F00A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)