

# Eaton XTCE012B10B

Catalog number: XTCE012B10B

Eaton XT IEC contactor, 12A, 220 Vac 50 Hz, 240 Vac 60 Hz, 1NO, 12A, Frame B, 45 mm, 50-60 Hz, 1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton XT IEC contactor	XTCE012B10B
<b>EAN</b>	<b>Product Length/Depth</b>
4015082768294	1.81 in
<b>Product Height</b>	<b>Product Width</b>
3.07 in	2.76 in
<b>Product Weight</b>	<b>Certifications</b>
.5 lb	UL Listed CSA Certified

## defaultTaxonomyAttributeLabel

### Contact configuration

1 NO

### Coil voltage

220-240 Vac, 50/60 Hz

### Series

XT IEC

### Type

Full voltage non-reversing contactor

### HP rating - max

1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @ 115,200,230/200,230,460,575 V)

### Continuous ampere rating

12 A

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Operation

Non-reversing

### Amperage Rating

12A

### Number Of Poles

Three-pole

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_B 2D PDF](#)

[XTCE\\_B 2D Drawing Xchange](#)

[XTCE\\_B 3D Inventor](#)

[XTCE\\_B 3D Model Xchange](#)

[XTCE\\_B AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Global Data Sheet - XTCE012B10B](#)

[Eaton Specification Sheet - XTCE012B10B](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)