

Eaton XTCE012B10C

Catalog number: XTCE012B10C

Eaton XT IEC contactor, 12A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 1NO, 12A, Frame B, 45 mm, 50-60 Hz, 1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE012B10C
EAN	Product Length/Depth
4015082768331	3 in
Product Height	Product Width
2 in	3 in
Product Weight	Compliances
.3 lb	CE Marked RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Contact configuration

1 NO

Coil voltage

415-480 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @ 115,200,230/200,230,460,575 V)

Continuous ampere rating

12 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

12A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_B 2D PDF](#)

[XTCE_B 3D Inventor](#)

[XTCE_B 2D Drawing Xchange](#)

[XTCE_B 3D Model Xchange](#)

[XTCE_B AutoCAD 2D Footprint](#)

Specifications and datasheets

[Global Data Sheet - XTCE012B10C](#)

[Eaton Specification Sheet - XTCE012B10C](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia