

Eaton XTCE012B10T

Catalog number: XTCE012B10T

Eaton XT IEC contactor, 12A, 24 Vac, 50-60 Hz, 1NO, 12A, Frame B, 45 mm, 50-60 Hz, 1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, , Screw terminals, FVNR



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE012B10T
EAN	Product Length/Depth
4015082768348	4.92913386 in
Product Height	Product Width
2.67716535 in	1.77165354 in
Product Weight	Compliances
.5 lb	RoHS Compliant CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

45 mm

Contact configuration

1 NO

Coil voltage

24 Vac, 50-60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)

Continuous ampere rating

12 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

12A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_B 3D Model Xchange](#)

[XTCE_B AutoCAD 2D Footprint](#)

[XTCE_B 2D PDF](#)

[XTCE_B 2D Drawing Xchange](#)

[XTCE_B 3D Inventor](#)

Specifications and datasheets

[Global Data Sheet - XTCE012B10T](#)

[Eaton Specification Sheet - XTCE012B10T](#)