

Eaton XTCF020B00A

Catalog number: XTCF020B00A

Eaton XT IEC contactor, 20A, 110 Vac 50 Hz, 120 Vac 60 Hz, ONO-ONC, 20A, Frame B, 45 mm, 50-60 Hz, 1, 2/3, 3, 10, 10 hp (1/3PH @115, 230/200, 230, 460, 575 V), Four-pole, , Screw terminals, FVNR



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCF020B00A
EAN	Product Length/Depth
4015082769673	2.75 in
Product Height	Product Width
2 in	3 in
Product Weight	Compliances
.48501698 lb	RoHS Compliant CE Marked
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

45 mm

Contact configuration

0 NO, 0 NC

Coil voltage

110-120 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

1, 2/3, 3, 10, 10 hp (1/3PH @115,230/200,230,460,575 V)

Continuous ampere rating

20 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

20A

Number Of Poles

Four-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCF_B 3D Inventor](#)

[XTCF_B 2D PDF](#)

[XTCF_B AutoCAD 2D Footprint](#)

[XTCF_B 3D Model Xchange](#)

[XTCF_B 2D Drawing Xchange](#)

[XTCF_B AutoCAD 2D Footprint \(mm\)](#)

Specifications and datasheets

[Global Data Sheet - XTCF020B00A](#)

[Eaton Specification Sheet - XTCF020B00A](#)