

Eaton XTCE018C10A

Catalog number: XTCE018C10A

Eaton XT IEC contactor, 18A, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO, 18A, Frame C, 45 mm, 50-60 Hz, 2, 2, 3/ 5, 5, 10, 15 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE018C10A
EAN	Product Length/Depth
4015082770013	4 in
Product Height	Product Width
2 in	3.5 in
Product Weight	Compliances
.4 lb	CE Marked RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

45 mm

Contact configuration

1 NO

Coil voltage

110-120 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

2, 2, 3/ 5, 5, 10, 15 hp (1/3PH @115,200,230/200,230,460,575 V)

Continuous ampere rating

18 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

18A

Number Of Poles

Three-pole

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTCE_C 3D Model Xchange

XTCE_C 2D Drawing Xchange

XTCE_C 2D PDF

XTCE_C AutoCAD 2D Footprint

Specifications and datasheets

Eaton Specification Sheet - XTCE018C10A

Global Data Sheet - XTCE018C10A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)